mont-bell

共通取扱説明書

ストリームグラス シリーズ

Stream Glasses Series


この度はお買いあげいただき、誠にありがとうございます。この取扱説明書(以下「本説明書」といいます)は本製品の正しい取扱方法を説明しています。ご使用の前に本説明書をよくお読みいただき、正しい使用方法をご確認ください。


なお、ご不明な点等ございましたら、販売店もしくは(株) モンベル カスタマー・サービスまでお問い合わせく ださい。 本説明書は大切に保管してください。

■ 特長

本製品は、視界が広く、風の巻き込みが少ない大型一眼レンズを使用した軽量サングラスです。一般的な曇り止め加工されたレンズと比較して約3~5倍の防曇効果が持続するアンチフォグシステムを搭載。また、日本人の顔にフィットするフレームの形状と調節式ノーズパッド(2段階)により、快適な装着感を実現しています。

■ 各部の名称





■ 安全上の注意 ぶずお読みください

◆ 場合により人が死亡または重傷を負う可能性が想定される内容です。 ■ 軽傷または物的損害が発生する頻度が高いことが想定される内容です。

- ○本商品は有害な太陽光の紫外線などを大幅にカットするよう作られています。強い衝撃などから目を保護するものではありません。サングラスの用途以外に使用しないでください。
- ○レンズのカラーによっては朝や夕方、トンネル内などで視界が悪くなる場合があります。特に自動車、バイクなどの運転時のご使用にはご注意ください。
- ○調光レンズは濃くなった状態から淡く戻るまでに時間がかかります。
- ○調光レンズは車のフロントガラスの種類により、紫外線遮断効果で色調および濃度の変化が低下する ことがあります。
- ○ご使用前に、必ず点検してください。老朽化や、レンズ、フレームに損傷がある場合はご使用にならないでください。

注意 人が傷害を負ったり物的損害の発生が想定される内容です。

- ○装着は鼻、こめかみ、耳の3点に均等にかかるように装着してください。また、必ず両手で装着してください。 片手で取り扱うと破損する恐れがあります。
- ○暖房器具など高温になるところに近づけたり、車中などに放置しないでください。レンズやフレームが変質、 変形する恐れがあります。
- ○机等に置く場合は必ずレンズ面を上向きに置いてください。レンズ面を下にすると傷等がつく原因になります。
- ○保管する際は傷がつくような金属などと一緒にしないでください。レンズなどに傷がつく恐れがあります。
- ○長期間使用しない場合は付属のセミハードケースに入れて保管してください。
- ○目や顔を負傷する場合があるので、接触等がおこる激しいスポーツで使用しないでください。
- ○目を痛める原因となりますので、太陽や強い光を直視しないでください。
- 使用中にアレルギー症状等が発生した場合はただちに使用を中止して医師に相談してください。
- ○シンナー等の有機系溶剤は変形・変色の原因となりますので使用しないでください。また、アルコールでお手入れをする場合はレンズ内側以外の箇所に使用しないでください。
- ○正しいお手入れ方法や保管方法を守ってください。

■ 使用前の点検 使用にあたっては、毎回必ず次のことを確かめてください。 異常が見られた場合は使用しないでください。

- □レンズやフレームに亀裂や変形などがないか
- □ノーズパットやテンプルの角度調整が適切か、また緩みなどがないか

■ 使用方法

○ ノーズパッドの角度調節方法

本製品のノーズパッドは2段階に調節することができます。

ご使用の前にズレなくフィットするよう調節してください。

○ ソフトケース ── ソフトケースはレンズ拭きとしてもご使用いただけます。

ノーズパッド

- 調光レンズについて (ストリームグラスBCのみ):

| 紫外線量によってレンズの色の濃度が変化するレンズです。紫外線量が多い晴れた日中では、レンズの色が濃くなり、紫外線 | 量が少ない夜間などではレンズ色が薄くなります。行動時間が長い縦走登山や自転車の長距離走行などに適したレンズです。

- ○紫外線を遮断するガラスなどで覆われた車内では濃度変化の機能は十分に発揮されません。
- ○レンズの濃度変化は気温の影響を受けます。気温が高いと発色が薄く、冬季など気温が低いと発色が濃くなり、また淡く戻るまでに時間がかかります。
- ○レンズの調光性能は徐々に低下します。使用の環境にもよりますが、2年程度の使用で、濃度の低下や色調の変化が生じます。これは紫外線の影響による経年劣化によるもので、修理はできません。なお、経年劣化により濃度が低下した状態でも紫外線をカットする性能は変わりません。

■ お手入れ方法 間違ったお手入れ方法や保管方法は本製品の寿命を縮めます。 使用後や保管時は以下の点を参考にしてください。

- ○レンズに水、海水、汗、化粧品等がついた状態で放置すると、変質の原因となります。使用後はレンズを水で軽く洗い流し、水分を柔らかい布で拭き取ったあと、自然乾燥してください。
- ○レンズに曇り止め液やはっ水液などを塗らないでください。本製品は優れた防曇 (曇り止め)機能を施していますが、市販されている曇り止め液やクリーナーはこの防曇性能を低下させる恐れがあります。 別売のグラスクリーナー (#1109122) も本製品の防曇性能を低下させるため、レンズの内側に使用しないでください。
- ○レンズの内側が汚れた場合は、市販の消毒用アルコール、希釈した中性洗剤などを使い、めがね拭き等の柔らかい布で軽くふき取ってください※レンズの内側以外の箇所は、変形・変色の原因となりますのでアルコールは使用せず、中性洗剤で洗ってください。

※レンズ内側の表面を蛍光灯の下で見た場合、表面に油膜のような模様が見えますが、蛍光灯の波長により見えるもので、ご使用に問題はありません。

○ソフトケースの汚れがひどい場合は中性洗剤で洗ってください。

■ 保管方法

- ○本製品を保管する際は付属のケースに収納し、保管中や携行中に硬いもの(金属品、ジッパー等)が レンズに直接触れないようにしてください。レンズに傷がつく原因となります。
- ○長時間外圧を加えると変形する場合があります。無理な状態で携行、保管しないでください。付属の セミハードケースに収納した状態でも、長時間外圧が加わると変形する恐れがあります。
- ○暖房器具の近くや車の中など、気温の高いところに置かないでください。変形する恐れがあります。
- ○高温多湿な場所に保管しないでください。レンズのコーティング剥離の原因となる恐れがあります。

■ アフターサービス

お買い求めいただきました本製品は万全を期して製造しておりますが、万一不備な点がございましたら、お買い求めいただいた販売店、もしくは下記の弊社窓口までご連絡ください。

製造上の欠陥による不具合の場合は無償で交換させていただきます。なお、修理、交換等の要否につきましては、弊社の裁量にて判断させていただきます。

なお、以下のような原因での破損、不良につきましては保証いたしませんのでご了承ください。

○本製品の誤った使用方法によるもの○間違ったお手入れ、保管方法、経年変化による素材劣化○乱暴な取り扱いによるもの○その他、製造上の欠陥以外の原因によるもの

破損時は弊社にて診断をして、修理が可能な場合はご要望により有償にて修理させていただきます。

■ 仕様

素材:(フレーム) 超弾性ナイロン樹脂 (レンズ) ポリカーボネート (ノーズパッド) 熱可塑性エラストマー (セミハードケース) E.V.A. (ソフトケース) ポリエステル

■ その他

本製品の仕様、デザインは予告なく変更されることがあります。また、重量などのスペックには誤差が生じる場合があります。

#式会社 モンベル 本社 〒550-0013 大阪市西区新町2-2-2 https://www.montbell.jp/ 商品についてのお問い合わせはカスタマー・サービスまで Tel.06-6531-3544 フリーコール: 0088-22-0031

mont-bell

User's Manual

Stream Glasses Series

Stream Glasses Series


Thank you for purchasing this product. Before using, please carefully read this manual for instructions on the proper care and usage of this product.


If you have any questions regarding this product, please contact Montbell Customer Service or the store of original purchase. Keep this manual for future reference.

Description

Large single lens provides a wide range of vision and helps reduce exposure to wind in a lightweight form. Achieves 3 to 5 times better anti-fogging performance compared to a standard anti-fogging treatment. Designed to offer a perfect fit for people with a shallower nose bridge, wider face, higher cheekbones and wider pupillary distance. The nose pads are adjustable to two positions.

Components





■ Safety Warnings!

Please read carefully.

WARNING! Under certain conditions, use of this product can result in injury, death, or property damage.

- This product is designed to protect eves from the harmful effects of the sun's ultraviolet light. This product does NOT protect the eyes from impacts.
- Ovisibility can be affected during twilight hours and in tunnels depending on the lens color. Take extra caution when driving.
- The photochromic lens takes time to transition from dark to light.
- The color and ability of the lens to darken may be affected by your car's windshield depending on how it filters ultraviolet light.
- OPrior to use, check the product's condition and stop using immediately if you notice any damage or irregularities.

CAUTION!

Under certain conditions, use of this product can result in injury or property damage.

- OMake sure that the glasses are in equal contact with the nose, temples and ears. Always take off and put on glasses with both hands. Using one hand may break glasses.
- To prevent deformation and damage to the glasses, do NOT store in a car or places subject to temperature extremes.
- ○To prevent damaging the lenses, always set the glasses down with lenses facing up.
- To prevent damage to the glasses, do NOT store with hard or metal objects or in any place that may possibly scratch the lenses.
- When storing for an extended period of time, store in the semi-hard case.
- ODO NOT use glasses for extreme physical activities. Glasses may cause injury to eyes or face.
- To prevent eve damage, do NOT look directly at the sun or strong lights.
- OStop using immediately if you notice an allergic reaction.
- Obo NOT clean with thinners or other organic solvents. May result in deformation or discoloration. When cleaning with alcohol, do NOT apply to areas other than the inside of the lens.
- OPlease follow proper care and storage instructions.

■ Prior to use, inspect this product for: Stop using immediately if you notice any irregularities.

Nose pad-

Cracks in lenses or frame

Proper fit of nose pads and temples, and for any loose parts

■ Directions

OAdjusting angle of nose pads

The nose pads are adjustable to two positions, providing a comfortable fit.

○Soft case

The soft case can also be used to clean the lenses.

Photochromic lenses (Stream Glasses BC)

Photochromic lenses transition from light to dark color based on exposure to ultraviolet light. The lens color will darken in bright sunlight and become lighter when there is less ultraviolet light, such as during dusk or night. These glasses are especially well suited for trekking and long bike rides.

The ability of the lens to darken is affected by UV coatings on cars or when inside buildings.

The ability of the lens to darken is affected by temperature. Generally, the lens will be darker in lower temperatures and will take longer to transition back to a lighter color.

Over time the color and ability of the lens to darken will be degraded (generally in about 2 years of use). This is a natural deterioration due to exposure to ultraviolet light and is not repairable. The UV protection performance of the lens remains unaffected even after losing its ability to darken.

Improper care and storage of this product can shorten its lifespan. Follow the recommendations below to extend the lifespan of your product.

ODO NOT allow the glasses to remain dirty after coming into contact with fresh water, salt water. sweat or makeup. After use, lightly wash the glasses with water and use a soft cloth to remove excess water, then allow to air dry.

ODO NOT apply any anti-fogging or water-repellent solutions to the lens. This product provides excellent anti-fogging performance, and commercially available cleaners and anti-fogging solutions may degrade this performance. Do NOT use the sold separately Glasses Cleaner (#1109122) on the inside of this product's lens as it will reduce the anti-fogging performance.

○If the inside of the lens is dirty, use commercially available alcohol or a diluted neutral detergent and gently wipe the lens with a soft cloth or glasses cleaning wipe. *Do NOT clean parts other than the inside of the lens with alcohol. May result in deformation and damage. Clean other parts with a neutral detergent.

*An oil film-like pattern is visible on the inner surface of the lens when viewed under a fluorescent light. This is due to the wavelength of fluorescent light and causes no effect on product performance.

OClean the soft case with a mild detergent when heavily soiled.

Storage

When storing the product, store in one of the included cases. Do NOT store or carry the product together with hard items (metal objects, zipper, etc.). May result in scratches to the lens.

To prevent deformation and damage to the glasses, do NOT apply pressure to the glasses for an extended period of time. Excessive pressure to the semi-hard case may damage the glasses inside. Be careful when carrying glasses around with you and when storing.

To prevent deformation and damage to the glasses, do NOT store in a car or places subject to temperature extremes.

OHigh heat and high humidity may cause the lens coating to peel.

■ Warranty

Montbell's warranty covers all defects in materials and workmanship to the original owner, for the lifetime of the product. If a product ever fails due to a manufacturing defect, Montbell will repair or replace the product at Montbell's discretion. This warranty does not cover damage(s) caused by accident, improper care, negligence, misuse, alterations or normal wear and tear. Damage(s) not covered under warranty will be repaired at a reasonable rate. If you would like to make a warranty inquiry, please contact Montbell Customer Service or the store of original purchase.

■ Specifications

Material: (Frame) nvlon resin (Lens) polycarbonate (Nose pad) TPU (Semi-hard case) E.V.A. (Soft case) polyester

> All product specifications and design are subject to change without prior notice. Actual product specifications may vary.

mont-bell Co..Ltd.

2-2-2 Shinmachi, Nishi-ku, Osaka 550-0013 JAPAN https://www.montbell.com/